











Gel-Pak Retention Labels

Gel-Pak has refined its Gel chemistry to provide a wide range of retention (tack) levels from an extremely low tack Gel for holding small polished optics to a high tack Gel for holding large ceramic substrates.

| Label | Retention Level | Description | Products | | | | | | |
|---|-----------------|---------------------|----------|----|----|----|----|----|-----|
| | | | AD | BD | CD | VR | PF | WF | DGL |
|  XT | XT | Ultra Low Tack Gel | ✓ | ✓ | ✓ | ✓ | ✓ | | ✓ |
|  XL | XL | Low Tack Gel | | | | ✓ | | | ✓ |
|  0 | X0 | Low Tack Gel | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
|  4 | X4 | Medium Tack Gel | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
|  5 | X5 | Medium Tack Gel | ✓ | ✓ | ✓ | | | | |
|  6 | X6 | High Tack Gel | ✓ | ✓ | ✓ | | | | |
|  8 | X8 | High Tack Gel | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
|  ER0 | ER0 | Low Tack ESD Gel | ✓ | ✓ | ✓ | | ✓ | ✓ | |
|  ER4 | ER4 | Medium Tack ESD Gel | ✓ | ✓ | ✓ | | ✓ | ✓ | |
|  ER6 | ER6 | Medium Tack ESD Gel | ✓ | ✓ | ✓ | | ✓ | ✓ | |
| 31398 Huntwood Avenue, Hayward, CA 94544-7818 Ph: (510) 576-2220, Fax: (510) 576-2282 www.gelpak.com | | | | | | | | | |