


Revision History			
Rev.	Description	By	Date
1	Initial Release	N/A	11/16/07
2	Changed tolerance from +/- 0.005" to 0.007". added note about tray orientation on fixture.	N/A	07/07/08
3	cell dim. .1755" is actually .180" chg to meet manuf. practice	PM	08/30/11



High Accuracy print placement required.
High Accuracy Registration = +/- 0.007"


Load tray onto fixture so that the cut corner is located lower left corner. See picture in job file for part to fixture orientation. Must use MicroVu for First Article & In Process Inspections.

Notes:

- 1) Cell Size: 0.180" x 0.180"
- 2) Line Weight: 0.017"

NOTICE OF PROPRIETARY RIGHTS IN DATA

THE DATA CONTAINED HEREIN IS PROPRIETARY TO GEL-PAK. THIS DATA SHALL NOT BE DUPLICATED, TRANSFERRED, MADE AVAILABLE TO, OR USED BY ANY THIRD PARTY FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY GEL-PAK.

		31398 Huntwood Ave. Hayward, CA 94544 (510) 576-2220 www.gelpak.com	
		Description: Gel-Pak Print# P-0192-HA (7X7 High Accuracy)	
Part # P-0192-HA		Rev: 3	
Dwg # P-0192-HA_rev.3		Date: 08/30/11	
Scale: 1:1	Dimensions: inches	Sheet: 1 of 1	